




"SILENT SENTRY" **ALARM PANELS** **For Medical Pipeline Systems**



"Silent-Sentry" Alarm Panels may be used in operating rooms, intensive care areas, or other locations where continuous monitoring of system pressure/vacuum is desired. Each "Signal-Gauge" indicator shows line pressure or vacuum, within normal operating range and activates a red warning light when system pressure or vacuum deviates from the tolerance allowed. Each panel includes: 115/24 VAC Transformer, Power on light, "Signal Gauge(s)," Push to Test Button, Warning Light and color coded service labels.

SPECIFICATIONS

Alarm panel shall operate in the following manner: "Signal-Gauge" registers pipeline pressure or vacuum within a pre-established normal range(1). When system pressure or vacuum deviates from normal range, "Signal-Gauge" activates a red warning light. When system returns to normal, light automatically turns off. Alarm panel shall include a continuous duty 115/24 V.A.C. transformer fused on the primary side. Transformer shall have a maximum output rating of .3 Amps at 24 volts. Alarm shall be provided with "power on" light and test button to check integrity of warning light circuits.

Each alarm shall include permanent, color-coded gas identification labels. Coverplate shall be 22 ga. stainless steel with brushed finish. Alarm panel box shall be 18 ga. steel with knockouts for electrical and piping connections.

Alarm shall be Puritan Product No. (2)_____or equal for the following services_____
(specify) (O₂, N₂O, Air, Vac., & N₂)

(1) Recommended operating range:


40 to 65 psig for Oxygen, Nitrous Oxide and Air per National Fire Protection Assoc. Pamphlet 56F.

140 to 190 psig for Nitrogen per NFPA 56F.

12" Hg. to maximum for Vacuum per Compressed Gas Assoc. Pamphlet P-2.1.

(2) Select Product No. from back page.


"SILENT SENTRY" ALARM PANELS



Single Service Panels

129183—0-100 psig Pressure
"Signal-Gauge"

129184—0-30" Hg. Vacuum
"Signal-Gauge"




Two Services*

129185—(2) 0-100 psig Pressure
"Signal-Gauges"

129186—(1) 0-100 psig Pressure
and (1) 0-30" Hg.
Vacuum "Signal-Gauges"

**Blank is provided for unused service location.*




Three Services

129187—(3) 0-100 psig Pressure
"Signal-Gauges"

129188—(2) 0-100 psig Pressure
and (1) 0-30" Hg.
Vacuum "Signal-Gauges"

129189—(2) 0-100 psig and (1)
0-300 psig (Nitrogen Only)
Pressure "Signal-Gauges"



Four Service

129190—(2) 0-100 psig Pressure,
(1) 0-30" Hg. Vacuum and
(1) 0-300 psig (Nitrogen
Only) Pressure
"Signal-Gauges"



Better Breathing Is Our Business

PURITAN-BENNETT CORPORATION

General Offices—Puritan-Bennett Building—Oak at Thirteenth,
Kansas City, Missouri 64106